






Audience Signal Light - ASL4-ND3

with Bluetooth Antenna (ASL4-ND3BT)







Limitimer®
 AUDIENCE SIGNAL LIGHT ASL4-ND3
 SWITCH SETTINGS
 (*=DEFAULT)

DISPLAY PROGRAMS				COUNT BEHAVIOR	CLOCK	N/A	CLOCK ENABLE		
	1	2	3	4	5	6	7	8	9
ON	*	*	*	*	* COUNT PAST 0:00	* 12 HOUR			DISPLAY CLOCK WHEN TIMER IS OFF
OFF					STOP AT 0:00	24 HOUR			DISPLAY BLANK WHEN TIMER IS OFF


WWW.DSAN.COM 516 625-5608




MODEL ASL4-ND3BT			
10	11	12	
*	*	*	
Settings to receive data from wireless timer model PRO-2000BT 10 Turn transceiver on/off 11+12 Bluetooth® communications channels. Match with switches 11 + 12 on timer			

Limitimer[®]


Relative Sizes of Components




PSL-20V



PRO-2000





PSL-20VF



ASL-2ND3

ASL-4



ASL-4ND3